

Valve ports

A complete assortment of rubber and PU Valve ports

Document produced by
Jonas Wall
2014-01-08

Valve ports

Valve port - Polyurethane (75 mm)



Item no. 60885

- Polyurethane
- Outer diameter: 75 mm
- Inner diameter: 33 mm
- Dual groove
- Fits all SI TECH valves

Valve port - Polyurethane (85 mm)



Item no. 60895

- Polyurethane
- Outer diameter: 85 mm
- Inner diameter: 33 mm
- Dual groove
- Fits all SI TECH valves

Valve ports

Valve port - Rubber



Item no. 60805

- Neoprene rubber
- Outer diameter: 100 mm
- Inner diameter: 33 mm
- Dual groove
- Fits all SI TECH valves

Valve port - Rubber (elevated rear flange)



Item no. 60810

- Neoprene rubber
- Outer diameter: 100 mm
- Inner diameter: 33 mm
- Dual groove
- Elevated rear flange
- Fits all SI TECH valves

Valve ports

Internal Valve port - Polyurethane



Item no. 60852-CUT

Valve port intended to be glued or welded on the inside of a drysuit.

- Polyurethane
- Outer diameter: 70 mm
- Inner diameter: 33 mm
- Can be glued or welded
- Fits all SI TECH valves

Weld nut - Polyurethane



Item no. 11032

For welded attachment of valves.

- Polyurethane
- Outer diameter: 64 mm
- Inner thread: M33 x 1,5mm
- Fits all SI TECH valves